






RoHS 2.0+HF







20006AN-000A-01T02	PACKING WITH SCREW
20006AN-000A-01T01	WITHOUT SCREW
DESCRIPTION	DESCRIPTION

SPECIFICATIONS:
1. RECOMMENDED TORQUE FORCE IS : 0.35 N·m.
2. THE REFERENCED PRODUCT SHALL BE COMPLIANT TO RoHS DIRECTIVE.


REV.	REVISION RECORD	DATE		GENERAL TOLERANCES		SCALE 1:1	NAME	DATE	PART NO.	DWG NO.				
A0	Initial release	2025.10.29		LINEAR	ANGLES	APPROVED	Jackie Tan	2026.06.16	20006AN-000A-01TXX	ENDE05				
A1	ADD PACKAGE SPEC	2025.11.13		0.0±0.25	X° REF±6°	DESIGNER	Halo.Wang	2026.06.16						
A2	Modify The Tolerance	2026.06.16		UNIT: MM	0.00±0.15	X° ±3°	DRAWN	Girder Liang	2026.06.16	TITLE R/A REC GUIDE PIN		REV	A2	SHEET

RoHS 2.0+HF




REV.	REVISION RECORD	DATE		GENERAL TOLERANCES		SCALE 1:1	NAME	DATE	PART NO.	DWG NO.				
A0	Initial release	2025.10.29		LINEAR	ANGLES	APPROVED	Jackie Tan	2026.06.16	20006AN-000A-01TXX	ENDE05				
A1	ADD PACKAGE SPEC	2025.11.13		0.0±0.25	X° REF±6°	DESIGNER	Halo.Wang	2026.06.16	TITLE R/A REC GUIDE PIN					
A2	Modify The Tolerance	2026.06.16		0.00±0.15	X° ±3°	DRAWN	Girder Liang	2026.06.16						
			UNIT: MM	0.00±0.08	X° X' ±2°						REV	A2	SHEET	2/3


RoHS 2.0+HF




① 将检验OK的良品35pcs依次放入吸塑盒中。



② 将20盘装了产品的吸塑盒依次堆叠并将1个空盘至于最上层，用PE膜缠绕好。



③ 纸箱底部先放置一块泡沫板，再将缠绕好的产品放入纸箱，顶部再放入一块泡沫板。



④ 胶带封箱

REV.	REVISION RECORD	DATE		GENERAL TOLERANCES		SCALE 1:1	NAME	DATE	PART NO.	DWG NO.				
A0	Initial release	2025.10.29		LINEAR	ANGLES	APPROVED	Jackie Tan	2026.06.16	20006AN-000A-01TXX	ENDE05				
A1	ADD PACKAGE SPEC	2025.11.13		0.0±0.25	X° REF±6°	DESIGNER	Halo.Wang	2026.06.16						
A2	Modify The Tolerance	2026.06.16		UNIT: MM	0.00±0.15	X° ±3°	DRAWN	Girder Liang						
			SIZE: A4	0.000±0.08	X° X' ±2°						REV	A2	SHEET	3/3